

BC28, Copper Deadend Clamp for Guy Wire, 2/0 Str - 4/0 Str

By Burndy
Catalog # BC28



For Guy Wire, 2/0 Str - 4/0 Str.

General

Catalog Number	BC28
Connector Type	Deadend
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013496

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.63 in
Dimension - Height fraction	2-3/8 in
Dimension - Height inch	2.375 in
Dimension - Height mm	60.3 mm
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Pad Width inch	1.13 in
Dimension - Pin Diameter fraction	1/2 in
Dimension - Pin Diameter inch	0.50 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Conductor Related

Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2/0 AWG-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - 7988](#)
[Specifications - BC28](#)