

BC30, Copper Deadend Clamp for Guy Wire, 4/0 Str - 300 kcmil, 5/8" Guy Wire

By Burndy
Catalog # BC30



4/0 AWG Str - 300 kcmil Copper; 5/8" Guy Wire

Features

- Supplied with silicon bronze U-bolt, nuts, and washers
- Saddle is made of high strength, corrosion resistant copper alloy

General

Catalog Number	BC30
Material	Copper Alloy, Cast
Plated	N
U Bolt Type	UB226
UPC	781810891001

Dimensions

Dimension - Bolt Size inch	3/8 in
Dimension - D inch	1.19 in

Conductor Related

Conductor Range	#4/0 AWG (Str) - 300 kcmil
-----------------	----------------------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - 7988](#)
- [Specifications - BC30](#)