



BD10D13G150 Flexible Copper Braid

By Burndy
Catalog # [BD10D13G150](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810204290
UPC 12 Digit	7818102042900

Dimensions

Dimension - L Length Overall mm	257 mm
Dimension - Length Overall inch	10.13 in
Length	10.13 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.