



## BD10N1TN 10 inch Flexible Copper Braid

By Burndy  
Catalog # [BD10N1TN](#)

Tin plated Flexible Copper Braid 10 inches long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BD10N1TN
Connector Type	Braid
Material	Copper
UPC	781810495551
UPC 12 Digit	7818104955511

### Dimensions

Dimension - L Length Overall	254 mm
mm	

Dimension - Length Overall	10 in
inch	
Length	10 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	12
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 1011198](#)  
[Specifications - BD10N1TN](#)