



BD11D25G96SV 11 inch Flexible Copper Braid

By Burndy
Catalog # [BD11D25G96SV](#)

Tin plated Flexible Copper Braid 11 inches long.



General

Catalog Number	BD11D25G96SV
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Silver
UPC	781810142042
UPC 12 Digit	7818101420422

Dimensions

Dimension - L Length Overall mm	286 mm
Dimension - Length Overall inch	11.25 in
Length	11.25 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10051543-01_A](#)
[Specifications - BD11D25G96SV](#)