



BD120G283TN Flexible Copper Braid

By Burndy
Catalog # [BD120G283TN](#)

Tinned copper flexible braid 120"x0.94"x0.13".



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810657911
UPC 12 Digit	7818106579111

Dimensions

Dimension - L Length Overall mm	3048
Dimension - Length Overall inch	120
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	120 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BD120G283TN-SPEC-EN | REV 5/2024