



## BD12G259TN 12 inch Flexible Copper Braid

By Burndy  
Catalog # [BD12G259TN](#)

Flexible Tin Copper Braid 12 inches long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BD12G259TN
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810493212
UPC 12 Digit	7818104932122

### Dimensions

Dimension - L Length Overall	305 mm
mm	
Dimension - Length Overall	12 in
inch	
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10108315](#)  
[Specifications - BD12G259TN](#)