



BD12TN Flexible Copper Braid

By Burndy
Catalog # [BD12TN](#)

Tinned copper flexible braid 12"x0.94"x0.13".



General

Catalog Number	BD12TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	621945176621
UPC 12 Digit	6219451766211

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BD12TN_MODEL-PDF](#)
- [3D Models - BD12TN_MODEL-STEP](#)
- [3D Models - BD12TN_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10044985](#)
- [Sales Drawings - Sales Drawing BD12TB](#)
- [Specifications - BD12TN](#)