



BD13T38 13 inch Flexible Copper Braid

By Burndy
Catalog # [BD13T38](#)

Flexible Tin Copper Braid 13 inches long.



General

Catalog Number	BD13T38
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	621945431133
UPC 12 Digit	6219454311333

Dimensions

Dimension - L Length Overall mm	330 mm
Dimension - Length Overall inch	13 in
Length	13 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	4500

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50047767](#)
- [Specifications - BD13T38](#)