



## BD14G191W Flexible Copper Braid

By Burndy  
Catalog # [BD14G191W](#)

Tin Plated Ferrules.



### General

Catalog Number	BD14G191W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810087282
UPC 12 Digit	7818100872822

### Dimensions

Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.00 in
Length	14 in

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BD14G191W-SPEC-EN | REV 6/2024