



BD16D50N1 16.50 inch Flexible Copper Braid

By Burndy
Catalog # [BD16D50N1](#)

Flexible Tin Copper Braid 16.50 inches long.



General

Catalog Number	BD16D50N1
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810550441
UPC 12 Digit	7818105504411

Dimensions

Dimension - L Length Overall mm	419 mm
Dimension - Length Overall inch	16.50 in
Length	16.5 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - se212372-01](#)
[Specifications - BD16D50N1](#)