



# BD18G127 18 inch Flexible Copper Braid

By Burndy  
Catalog # [BD18G127](#)

Flexible Tin Copper Braid 18 inches long.

## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	BD18G127
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Plating Type	Tin
UPC	781810443057
UPC 12 Digit	7818104430577



## Dimensions

Dimension - L Length Overall	457 mm
Dimension - Length Overall	18.00 in
Length	18 in

## Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

## Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30018577](#)  
[Specifications - BD18G127](#)



A Hubbell brand