



## BD18G80 18 inch Flexible Copper Braid

By Burndy  
Catalog # [BD18G80](#)

Flexible Tin Copper Braid 18 inches long.



### General

Catalog Number	BD18G80
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Plating Type	Tin
UPC	781810199800
UPC 12 Digit	7818101998000

### Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	4800

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50047629](#)  
[Specifications - BD18G80](#)