



BD18NB 18 inch Flexible Copper Braid

By Burndy
Catalog # [BD18NB](#)

Flexible Tin Copper Braid 18 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BD18NB
Connector Type	Rope lay
Material	Copper
Plated	Y
UPC	781810675069
UPC 12 Digit	7818106750699

Dimensions

Dimension - L Length Overall mm	457 mm
------------------------------------	--------

Dimension - Length Overall inch	18.00 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	3200

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50047825](#)
- [Specifications - BD18NB](#)