



# BD20U 20 inch Flexible Copper Braid

By Burndy  
Catalog # [BD20U](#)

Flexible Tin Copper Braid 20 inches long.



## General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810199145
UPC 12 Digit	7818101991455

## Dimensions

Dimension - L Length Overall mm	508 mm
Dimension - Length Overall inch	20.00 in
Length	20 in

## Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 10044985-01](#)



A proud member of the Hubbell Family.