



BD21G162TN Flexible Copper Braid

By Burndy

Catalog # [BD21G162TN](#)

Tin Plated Ferrules.



General

Catalog Number	BD21G162TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810078372
UPC 12 Digit	7818100783722

Dimensions

Dimension - L Length Overall mm	533 mm
Dimension - Length Overall inch	21.00 in
Length	21 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BD21G162TN](#)



A Hubbell brand