



## BD24 Flexible Copper Braid, 24 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction, 24 IN L

By Burndy  
Catalog # [BD24](#)

Flexible Copper Braid, 24 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction, 24 IN L.

### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

### General

Catalog Number	BD24
Connector Type	Braid
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
Sub Brand	BRAID JUMPER
Type	B, Flexible
UPC	781810806999
UPC 12 Digit	7818108069999

### Dimensions

Dimension - D inch	2.50 in
--------------------	---------



Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch Length	0.94 in 24 in

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1

### Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)  
[Sales Drawings - 10044985](#)  
[Specifications - BD24](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BD24-SPEC-EN | REV 10/2024