



## BD24G159U Flexible Copper Braid

By Burndy  
Catalog # [BD24G159U](#)

Undrilled Ferrules.



### General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810205242
UPC 12 Digit	7818102052422

### Dimensions

Length	24 in
--------	-------

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BD24G159U-SPEC-EN | REV 1/2024