



## BD24G188 Flexible Copper Braid 24 in Long

By Burndy  
Catalog # [BD24G188](#)

Flexible Copper Braid 24 in Long.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810077887
UPC 12 Digit	7818100778877

### Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Length	24 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2250

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD208278-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BD24G188-SPEC-EN | REV 5/2024