



BD30N Flexible Copper Braid 30 in Long

By Burndy
Catalog # [BD30N](#)

Flexible Copper Braid 30 in Long.



General

Catalog Number	BD30N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810127896
UPC 12 Digit	7818101278966

Dimensions

Dimension - L Length Overall mm	762 mm
Dimension - Length Overall inch	30.00 in
Length	30 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10045735-01_D](#)
[Specifications - BD30N](#)