



BD32CG2 Flexible Copper Braid

By Burndy
Catalog # [BD32CG2](#)

Flexible Copper Braid.



General

Catalog Number	BD32CG2
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810421192
UPC 12 Digit	7818104211922

Dimensions

Dimension - L Length Overall mm	813 mm
Dimension - Length Overall inch	32.00 in
Length	32 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BD32CG2-SPEC-EN | REV 6/2024