



## BD32D25G285TN Tin Plated Copper Braid 32.25 in Long

By Burndy  
Catalog # [BD32D25G285TN](#)

Tin Plated Copper Braid 32.25 in Long.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BD32D25G285TN
Connector Type	Braid
Material	Copper
UPC	621945430983
UPC 12 Digit	6219454309833

### Dimensions

Dimension - L Length Overall	819 mm
mm	

Dimension - Length Overall	32.25 in
inch	
Length	32.25 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50050407](#)
- [Specifications - BD32D25G285TN](#)