



BD36GGKIT Flexible Copper Braid

By Burndy

Catalog # [BD36GGKIT](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number BD36GGKIT
Connector Type Braid

Material	Copper
UPC	781810675274
UPC 12 Digit	7818106752744

Dimensions

Length	36 in
--------	-------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BD36GGKIT](#)