



BD36LT12 Flexible Copper Braid 36 in Long

By Burndy
Catalog # [BD36LT12](#)

Flexible Copper Braid 36 in Long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BD36LT12
Connector Type	Braid
Material	Copper
UPC	621945450257
UPC 12 Digit	6219454502577

Dimensions

Dimension - L Length Overall	914 mm
Dimension - Length Overall	36.00 in
inch	
Length	36 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50062307](#)
[Specifications - BD36LT12](#)