

# BD36NTN Tin Plated Copper Braid 36 in Long

By Burndy  
Catalog # [BD36NTN](#)



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	BD36NTN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810203293
UPC 12 Digit	7818102032933

## Dimensions

Dimension - L Length Overall	914 mm
mm	

Dimension - Length Overall	36.00 in
inch	
Length	36 in

## Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	No

## Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10045735-01\\_D](#)  
[Specifications - BD36NTN](#)