



## BD38N Flexible Copper Braid 38 in Long

By Burndy  
Catalog # [BD38N](#)

Flexible Copper Braid 38 in Long.



### General

Catalog Number	BD38N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810205525
UPC 12 Digit	7818102055255

### Dimensions

Dimension - L Length Overall mm	965 mm
Dimension - Length Overall inch	38.00 in
Length	38 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10045735-01\\_D](#)  
[Specifications - BD38N](#)