



## BD42TN Flexible Copper Braid

By Burndy  
Catalog # [BD42TN](#)

Tinned copper flexible braid 42"x0.94"x0.13".



### General

Catalog Number	BD42TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810496398
UPC 12 Digit	7818104963988

### Dimensions

Dimension - L Length Overall mm	1067
Dimension - Length Overall inch	42
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	42 in

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	3
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BD42TN](#)