



BD52 Flexible Copper Braid 52 in Long

By Burndy
Catalog # [BD52](#)

Flexible Copper Braid 52 in Long.



General

Catalog Number	BD52
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810078129
UPC 12 Digit	7818100781299

Dimensions

Dimension - L Length Overall mm	1321 mm
Dimension - Length Overall inch	52.00 in
Length	52 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10044985](#)
[Specifications - BD52](#)



A Hubbell brand