



BD56G285TN Tin Plated Copper Braid 56 in Long

By Burndy
Catalog # [BD56G285TN](#)

Tin Plated Copper Braid 56 in Long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

| | |
|----------------|---------------|
| Catalog Number | BD56G285TN |
| Connector Type | Braid |
| Material | Copper |
| UPC | 621945431317 |
| UPC 12 Digit | 6219454313177 |

Dimensions

| | |
|------------------------------|---------|
| Dimension - L Length Overall | 1422 mm |
| mm | |

| | |
|----------------------------|----------|
| Dimension - Length Overall | 56.00 in |
| inch | |
| Length | 56 in |

Electrical Ratings

| | |
|---------------------------|-------|
| Rating - Indoor Amperage | 190 A |
| Rating - Outdoor Amperage | 225 A |

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 1680 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50050407](#)
[Specifications - BD56G285TN](#)