



BD6G175 Flexible Copper Braid 6 in Long

By Burndy
Catalog # [BD6G175](#)

Flexible Copper Braid 6 in Long.



General

Catalog Number	BD6G175
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810062135
UPC 12 Digit	7818100621355

Dimensions

Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Length	6 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30026368](#)



A proud member of the Hubbell Family.