



## BD6G53 Flexible Copper Braid 6 in Long

By Burndy

Catalog # [BD6G53](#)

Flexible Copper Braid 6 in Long.



### General

Catalog Number	BD6G53
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Plating Type	Tin
UPC	781810201305
UPC 12 Digit	7818102013055

### Dimensions

Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Length	6 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50060325](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BD6G53-SPEC-EN | REV 6/2024