



BD70TN Flexible Copper Braid

By Burndy
Catalog # [BD70TN](#)

Tinned copper flexible braid 70"x0.94"x0.13".



General

Catalog Number	BD70TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810496381
UPC 12 Digit	781810496381

Dimensions

Dimension - L Length Overall mm	1778
Dimension - Length Overall inch	70
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	70 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BD70TN](#)



A Hubbell brand