



## BD72GTN Flexible Copper Braid

By Burndy  
Catalog # BD72GTN

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BD72GTN
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	621945457232

UPC 12 Digit 6219454572322

### Dimensions

Length 72 in

### Electrical Ratings

Rating - Indoor Amperage 190  
Rating - Outdoor Amperage 225

### Certifications And Compliance

Certification - CSA Approved Yes  
Industry Standard(s) UL467  
Standards - Industry Standards Met UL467  
Standards - RoHS Compliance CM  
Status

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50060399](#)  
[Specifications - BD72GTN](#)