



BD88 Flexible Copper Braid 88 in Long

By Burndy
Catalog # [BD88](#)

Flexible Copper Braid 88 in Long.



General

| | |
|---------------------------------------|---------------|
| Catalog Number | BD88 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| Plating Type | Tin |
| UPC | 781810206218 |
| UPC 12 Digit | 7818102062188 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 2235 mm |
| Dimension - Length Overall inch | 88.00 in |
| Length | 88 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 190 |
| Rating - Outdoor Amperage | 225 |

Certifications And Compliance

| | |
|--------------------------------|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards | UL467 |
| Met | |
| Standards - RoHS Compliance | EX |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10044985](#)
[Specifications - BD88](#)



A Hubbell brand