



BD9G175TN Flexible Copper Braid

By Burndy
Catalog # [BD9G175TN](#)

Tin Plated Ferrules.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810205983
UPC 12 Digit	7818102059833

Dimensions

Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9.00 in
Length	9 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50017785](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BD9G175TN-SPEC-EN | REV 1/2024