



BDALHC22600, Power Distribution Block Adder

By Burndy

Catalog # [BDALHC22600](#)

840 Amps; #2 AWG - 600 kcmil Run & Tap.



General

Catalog Number	BDALHC22600
Installation Torque Recommended in-lb	600 in-lb
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810651971
UPC 12 Digit	7818106519711

Dimensions

Dimension - Height inch	3.55 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

Electrical Ratings

Amperage Rating	840 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;4
Conductor - AL Str Run Range	2-600
Conductor - AL Str Tap	2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;4
Conductor - AL Str Tap Range	2-600
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500;550;6
Conductor - Copper Str Run Range	2-600
Conductor - Copper Str Tap	2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500;550;6
Conductor - Copper Str Tap Range	2-600

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	18
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
- [Sales Drawings - 50020385](#)
- [Specifications - BDALHC22600](#)



A Hubbell brand