



# BDASHC112/01, Power Distribution Block Adder

By Burndy  
Catalog # [BDASHC112/01](#)

Terminal Block, 3.08 in L, .93 in W, Glass Filled Ploycarbonate, AWG 14 - 2/0 (Run), AWG 14 - 2/0 (Tap).



## Application

Industrial control feeder, HVAC system and wire ways

## General

|                    |               |
|--------------------|---------------|
| EU RoHS Indicator  | Yes           |
| Insulation         | Y             |
| Material           | Aluminum      |
| Number Of Poles    | Adder         |
| Plated             | N             |
| Plating Type       | Tin           |
| Sub Brand          | VERSI-POLE    |
| Temperature Rating | 194           |
| Trade Name         | VERSIPOLE™    |
| Type               | BDA           |
| UPC                | 781810645475  |
| UPC 12 Digit       | 7818106454755 |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 2.81 in |
| Dimension - L Length Overall mm | 78 mm   |
| Dimension - Length Overall inch | 3.08 in |
| Dimension - Width inch          | 0.93 in |
| Dimension - Width mm            | 24 mm   |

## Electrical Ratings

|                          |       |
|--------------------------|-------|
| Amperage Rating          | 175 A |
| Rating - Minimum Voltage | 600   |

## Conductor Related

|                                  |                                    |
|----------------------------------|------------------------------------|
| Conductor - AL Str Run           | 12;10;8;6;4;3;2;1;1/0;2/0          |
| Conductor - AL Str Run Range     | 12-2/0                             |
| Conductor - AL Str Tap           | 12;10;8;6;4;3;2;1;1/0;2/0          |
| Conductor - AL Str Tap Range     | 12-2/0                             |
| Conductor - Copper Str Run       | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Run Range | 14-2/0                             |
| Conductor - Copper Str Tap       | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Tap Range | 14-2/0                             |

## Certifications And Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

## Logistics

|                       |    |
|-----------------------|----|
| Carton Quantity       | 36 |
| Minimum Pack Quantity | 1  |

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Small\\_Lineart](#)
- [Sales Drawings - 50020385](#)



A proud member of the Hubbell Family.