

BDBC0VER1, Power Distribution Block Cover

By Burndy
Catalog # BDBC0VER1



POWER DISTRIBUTION BLOCKS.

General

Catalog Number	BDBC0VER1
Material	Polycarbonate
Number Of Poles	2
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810115336
UPC 12 Digit	7818101153366

- CU C Str-Run
- AL C Str-Tap
- CU C Str-Tap

Dimensions

Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.36 in
Dimension - Width inch	2.90 in
Dimension - Width mm	74 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run
----------------	--

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BDBC0VER1_MODEL-PDF](#)
- [3D Models - BDBC0VER1_MODEL-STEP](#)
- [3D Models - BDBC0VER1_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BDB_LineArt](#)
- [Sales Drawings - 30014574](#)
- [Specifications - BDBC0VER1](#)