



## BDBCORDER2, Power Distribution Block Cover

By Burndy  
Catalog # BDBCORDER2



POWER DISTRIBUTION BLOCKS.

### General

Catalog Number	BDBCORDER2
Material	Polycarbonate
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810115374
UPC 12 Digit	7818101153744

### Dimensions

Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.91 in
Dimension - Width inch	2.03 in
Dimension - Width mm	52 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>
----------------	---

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - BDBCORDER2\\_MODEL-PDF](#)
- [3D Models - BDBCORDER2\\_MODEL-IGES](#)
- [3D Models - BDBCORDER2\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BDB\\_LineArt](#)
- [Sales Drawings - 30025808](#)
- [Specifications - BDBCORDER2](#)