



BDBCover2, Power Distribution Block Cover

By Burndy
Catalog # [BDBCover2](#)



POWER DISTRIBUTION BLOCKS.

General

Catalog Number	BDBCover2
Material	Polycarbonate
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810115374
UPC 12 Digit	7818101153744

Dimensions

Dimension - Height mm	0 mm
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.91 in
Dimension - Width inch	2.03 in
Dimension - Width mm	52 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none">AL C Str-RunCU C Str-RunAL C Str-Tap
----------------	--

- CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BDBCover2_MODEL-IGES](#)
- [3D Models - BDBCover2_MODEL-STEP](#)
- [3D Models - BDBCover2_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BDB_LineArt](#)
- [Sales Drawings - 30025808](#)
- [Specifications - BDBCover2](#)