

## BDBLCS3KA, Flex Rated Power Distribution Block Adder

By Burndy  
Catalog # BDBLCS3KA

Distribution block, One pole Finger Safe 6 AWG-350 kcmil (Run).



### Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

### General

Catalog Number	BDBLCS3KA
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	621945448872
UPC 12 Digit	6219454488722

### Dimensions

Dimension - Height inch	4.12
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	141
Dimension - Length Overall inch	5.54
Dimension - Width mm	77 mm

### Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

### Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	14 AWG - 2/0 AWG
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	14 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	720

### Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - 50130772 - Adder Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50063029](#)  
[Specifications - BDBLCS3KA](#)