



BDBLCS4T2, 2-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBLCS4T2](#)

POWER DISTRIBUTION BLOCKS.



General

Catalog Number	BDBLCS4T2
Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810676035
UPC 12 Digit	7818106760355

Dimensions

Dimension - Height inch	4.15
Dimension - L Length Overall mm	157
Dimension - Length Overall inch	6.17

Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	6 AWG - 350 kcmil
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	6 AWG - 350 kcmil
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	216

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50059695](#)
[Specifications - BDBLCS4T2](#)