



BDBLCS6V3FS, 3-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy
Catalog # [BDBLCS6V3FS](#)



POWER DISTRIBUTION BLOCKS.

General

Catalog Number	BDBLCS6V3FS
Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810676912
UPC 12 Digit	7818106769122

Dimensions

Dimension - Height inch	4.15
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	231
Dimension - Length Overall inch	9.09

Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Run Range	4 AWG - 500 kcmil
Conductor - AL Str Tap Range	4 AWG - 500 kcmil
Conductor - Copper Str Run Range	4 AWG - 500 kcmil
Conductor - Copper Str Tap Range	4 AWG - 500 kcmil
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	144

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50059695](#)
- [Specifications - BDBLCS6V3FS](#)