



Image represents single pole

BDBLCS7X2DW, Large Flex Rated Power Distribution Block

By Burndy

Catalog # [BDBLCS7X2DW](#)

POWER DISTRIBUTION BLOCK, 2 POLE 600V AL9CU, RUN:(5) 500-4 TAP:(5) 500-4.



Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of V0
- Double-Wide Series

General

Catalog Number	BDBLCS7X2DW
Connector Type	Power Distribution Block
Material	Aluminum
Trade Name	VERSIPOLE™
UPC	621945518476

Dimensions

Weight 5.68 lb

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	168

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50081549](#)
[Specifications - BDBLCS7X2DW](#)