



BDBLCS8Y3, Large Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBLCS8Y3](#)

POWER DISTRIBUTION BLOCK, 3 POLE, 600V, AL9CU, Run: (2)
#4-600, (2) Tap: #4-600

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of V0
- Double-Wide Series

General

Catalog Number BDBLCS8Y3



*Representative Image

Material	Aluminum
Trade Name	VERSIPOLE™
UPC	621945549814

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	Yes

Logistics

Carton Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Sales Drawings - 50059695](#)