

BDBLHC1123503, 3-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC1123503](#)



Terminal block covers, AWG 6 - 350 kcmil (Run), AWG 14 - 4 (Tap), Power Distribution Block

Application

Industrial control feeder, HVAC system and wire ways

General

Catalog Number	BDBLHC1123503
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE™
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810645680
UPC 12 Digit	7818106456800

Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	200
Dimension - Length Overall inch	7.89
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;350;4;530
Conductor - AL Str Run Range	6-350

Conductor - AL Str Tap	12;10;8;6;4
Conductor - AL Str Tap Range	12-4
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4
Conductor Type	<ul style="list-style-type: none"> AL C Str-Run CU C Str-Run AL C Str-Tap CU C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
[Sales Drawings - 50018991](#)
[Specifications - BDBLHC1123503](#)