



BDBLHC2125001, 1-Pole Power Distribution Block

By Burndy
Catalog # [BDBLHC2125001](#)



Al Power Distribution Block, 1 Pole, 760 Amp/Pole, #4 AWG-500 kcmil(Run), #14-#4 AWG(Tap).

General

Catalog Number	BDBLHC2125001
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645888
UPC 12 Digit	7818106458888

Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	69
Dimension - Length Overall inch	2.73
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	12;10;8;6;4
Conductor - AL Str Tap Range	14-4

Conductor - Copper Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;4-500
Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	18
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Images\) - BUR_VERSIPOLE_Large_Lineart](#)
- [Sales Drawings - 50018991](#)
- [Specifications - BDBLHC2125001](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BDBLHC2125001-SPEC-EN | REV 10/2024