



## BDBLHC2125002, 2-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC2125002](#)

Al Power Distribution Block, 2 Pole, 760 Amp/Pole, #4 AWG-500 kcmil(Run), #14-#4 AWG(Tap).



### General

Catalog Number	BDBLHC2125002
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810646588
UPC 12 Digit	7818106465888

### Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	135
Dimension - Length Overall inch	5.73
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

### Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477-500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	12;10;8;6;4
Conductor - AL Str Tap Range	14-4

Conductor - Copper Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;
Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	9
Minimum Pack Quantity	1

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Images\) - BUR\\_VERSIPOLE\\_Large\\_Lineart](#)
- [Sales Drawings - 50018991](#)
- [Specifications - BDBLHC2125002](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BDBLHC2125002-SPEC-EN | REV 10/2024