



# BDBLHC223502, 2-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC223502](#)



Power Distribution Block,AWG 6 - 350 kcmil (Run), AWG 6 - 350 kcmil (Tap).

## General

Catalog Number	BDBLHC223502
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645949
UPC 12 Digit	7818106459499

## Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	135
Dimension - Length Overall inch	5.73
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

## Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600

## Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350
Conductor - AL Str Tap Range	6-350
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300
Conductor - Copper Str Tap Range	6-350
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	9
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Large\\_Lineart](#)
- [Sales Drawings - 50018991](#)
- [Specifications - BDBLHC223502](#)