



BDBLHC226003, 2-Pole Power Distribution Block

By Burndy
Catalog # [BDBLHC226003](#)



Power Distribution Block,AWG 2 - 600 kcmil (Run), AWG 2 - 600 kcmil (Tap).

General

Catalog Number	BDBLHC226003
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	N
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810652008
UPC 12 Digit	7818106520088

Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	200
Dimension - Length Overall inch	7.89
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

Electrical Ratings

Amperage Rating	840 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477.5;500;556;600
------------------------	---

Conductor - AL Str Run Range	2-600
Conductor - AL Str Tap	2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;
Conductor - AL Str Tap Range	2-600
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;50
Conductor - Copper Str Run Range	2-600
Conductor - Copper Str Tap	2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;50
Conductor - Copper Str Tap Range	2-600

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
- [Sales Drawings - 50018991](#)
- [Specifications - BDBLHC226003](#)

